


Film, Metallized Polypropylene, Safety, F863, 0.68 uF, 10%, 310 V, 110C, Lead Spacing = 22.5mm



**Dimensions**

L	26.5mm +0.3mm
H	18.5mm +0.1mm
T	10mm +0.2mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

**Packaging Specifications**

Packaging:	Bulk
Packaging Quantity:	300

**General Information**

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	F863
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL, CQC

**Specifications**

Capacitance:	0.68 uF
Capacitance Tolerance:	10%
Voltage AC:	310 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.2% 1KHz
Insulation Resistance:	10 GOhms
Max dVdt:	200 V
Safety Class:	X2