

Material number	0 603 672 100
EAN	3165140791830
Baretool number	3603F72100
2 x 1.5 V LR03 AAA	✓
Protective case	✓



Technical data

Technical data

Laser diode	635 nm
Laser class	2
Measurement range	0,05 – 30,00 m
Measurement accuracy, typical	± 2,0 mm
Measurement time, typical	0,5 s
Measurement time, max.	4 s
Battery	2 x 1.5 V LR03 (AAA)
Automatic deactivation	5 mins
Weight	0,08 kg



Functions

Area, volume calculation	✓
Addition, subtraction	✓
Continuous measurement	✓
Distance measurement	✓

Sales information

Positioning

- Your measuring results at a glance!

User benefit

- Precise measurement of distances up to 30 m with laser technology
- Conveniently document measuring results via Bluetooth with the Bosch PLR measure&go app
- Equipped with a high-quality colour display for optimum readability of the measuring results

Other features

- Easy calculation of distances, areas and volumes thanks to integrated measuring functions
- Measuring from front and back edge
- Compact tool design – fits in any pocket
- Continuous measurement mode with min/max function
- Addition and subtraction of measuring results