



Main

Product or component type	Contactor
Range of product	8502S
Contact application	Non-reversing
NEMA size	2
Rated power in HP	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
NEMA degree of protection	Not rated (open device)
Control type	No control units
Control circuit	Separate control circuit
Control type	No control units
Provided equipment	Fuse not supplied
Control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Local signalling	No indicator
Auxiliary contact composition	Without
Poles description	3P
Phase	3 phases
Line Rated Current	45 A
Product certifications	CSA UL listed
System Voltage	600 V AC
Electrical connection	Screw clamp terminals

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
----------	------------------------------------

GTIN	00785901881612
Nbr. of units in pkg.	1
Package weight(Lbs)	5.719999999999998
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------