



Heat Gun

With Adjustable Temperature Control



Temperature Dial

- Easy temperature selection



Airflow Switch

- Alternate between high and low airflow settings



Nozzle Attachments

- Includes 3 nozzle attachments to direct airflow as needed

Powerful Heat Application

Aven's Heat Gun with Adjustable Temperature Control features an easy-to-read, simple to use turn dial to select your temperature range. The power switch offers high and low airflow settings that heat up quickly for use. Features a convenient flip-out stand to position the nozzle vertically along a work bench, perfect for applications where operators are required to use both hands.

AVEN HEAT GUN 1500W w/ ADJUSTABLE TEMPERATURE CONTROL

Item #	17601
Weight	2.05 lbs
Voltage	120V / 1500W / 60Hz
Power Output	Low – 800W / High – 1500W
Temperature	Low: 50° C – 350° C / High: 200° – 500° C
Airflow	450L/min



Heat Gun

With Digital Temperature Control



Digital Temperature Dial

- Easy temperature selection



Airflow Switch

- Alternate between high and low airflow settings



Nozzle Attachments

- Includes 3 nozzle attachments to direct airflow as needed

Powerful Heat Application

Aven's Heat Gun With LCD Display offers precise heat control with a sharp LCD display. Exact temperatures in increments of 10 degrees can be chosen using the temperature controls on the back of the unit. Features high and low airflow settings, and is designed to use either by hand or placed vertically on a work bench. Includes 3 nozzle attachments.

AVEN HEAT GUN 1500W w/ DIGITAL TEMPERATURE CONTROL

Item #	17602
Weight	2.15 lbs
Voltage	120V / 1500W / 60Hz
Power Output	Low – 800W / High – 1500W
Temperature	Low: 100° C – 300° C / High: 300° – 650° C
Airflow	450L/min