


Aluminum Electrolytic, 85C, ALP22, 4700 uF, 20%, 40 V, -40/+85C



**Dimensions**

D	25mm +/-1mm
L	45mm +/-2mm
S	12.5mm +/-0.1mm
LL	7.5mm +/-0.5mm
F	1.3mm

**Packaging Specifications**

Weight:	39 g
Sleeving:	Yes
Packaging:	Bulk

**General Information**

Dielectric:	Aluminum Electrolytic
Series:	ALP22
Description:	Solder Pin, Aluminum Electrolytic
Features:	Solder Pin
RoHS:	Yes
Lead:	3 Pin Solder
Notes:	Dimensions D And L Include Sleeving

**Specifications**

Capacitance:	4700 uF
Capacitance Tolerance:	20%
Voltage DC:	40 VDC, 46 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	12000 Hrs
Leakage Current:	1128 uAmps (5min 20C)