



FEATURES:

- Converts BNC cables with male connectors to alligator clips for test versatility
- BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance
- BNC center contact is gold plated Beryllium Copper for corrosion resistance, low contact resistance and long insertion life
- Alligator clips attach to terminals up to .300" diameter

MATERIALS:

BNC: Nickel plated brass

Center Contact: Gold plated Beryllium Copper

Wire: 18 AWG, PVC

Marking: "POMONA 2630"

Alligator Clips: Nickel plated steel

Flex Boot: Vinyl

RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 150VRMS Max.

Operating Temperature: +50°C (+122°F) Max

ORDERING INFORMATION: Model 2630

All dimensions are in inches.

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90313 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com