


Aluminum Electrolytic, 85C, ALT22, 0.01 F, 20%, 63 V, -40/+85C



General Information	
Dielectric:	Aluminum Electrolytic
Series:	ALT22
Description:	Solder Tag, Aluminum Electrolytic
Features:	Solder Tag
RoHS:	Yes
Lead:	2 Flying Leads Solder Tags
Notes:	Dimensions D And L Include Slewing

Dimensions	
D	35mm +/-1mm
L	55mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Specifications	
Capacitance:	0.01 F
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	18000 Hrs
Leakage Current:	3780 uAmps (5min 20C)

Packaging Specifications	
Weight:	75 g
Slewing:	Yes
Packaging:	Bulk