


Ceramic, AxiMax, 0.1 uF, 20%, 50 V, Z5U, AxiMax, Commercial Standard



Dimensions

D	2.31mm MAX
L	4.32mm MAX
LL	25.4mm +0.025/-0.076mm
F	0.51mm +0.025/-0.076mm

Packaging Specifications

Packaging:	T&R, 305mm
Packaging Quantity:	5000

General Information

Series:	AxiMax
Description:	AxiMax, Commercial Standard
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Halogen Free:	Yes

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	20%
Voltage DC:	50 VDC
Dielectric Withstanding Voltage:	125 V
Temperature Range:	+10/+85C
Temperature Coefficient:	Z5U
Dissipation Factor:	4% 25C
Aging Rate:	7% Loss/Decade Hour
Insulation Resistance:	1 GOhms