



### FEATURES:

- Converts BNC cables with male connectors to Minigator test clips for test versatility
- BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance
- BNC center contact is gold plated Beryllium Copper for corrosion resistance, low contact resistance and long insertion life
- Minigator clips attach to terminals up to .187" diameter

### MATERIALS:

BNC: Nickel plated Brass

Center Contact: Gold plated Beryllium Copper

Wire: 20 AWG, PVC Insulated

Marking: "POMONA 2631"

Minigators: Nickel plated steel,

Spring: stainless steel

Flex Boot: Vinyl

### RATINGS:

Operating Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 150VRMS Max.

Operating Temperature: +50°C (+122°F) Max.

**ORDERING INFORMATION:** Model 2631

All dimensions are in inches.

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360  
Technical Assistance: 800-241-2060

PomonaACCESS 90314 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)