

**KEMET Part Number: C0402C106M7PACTU**  
(C0402C106M7PAC7867)

Ceramic, Commercial-(CxxxxC), 10 uF, 20%, 4 V, 0402, X5R, SMD, MLCC, Temperature Stable, Class II



**Dimensions**

<b>L</b>	1mm +/-0.2mm
<b>W</b>	0.5mm +/-0.2mm
<b>T</b>	0.5mm +/-0.20mm
<b>S</b>	0.3mm MIN
<b>B</b>	0.3mm +/-0.1mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Paper Tape
<b>Packaging Quantity:</b>	10000

**General Information**

<b>Style:</b>	SMD Chip
<b>Series:</b>	Commercial-(CxxxxC)
<b>Chip Size:</b>	0402
<b>Description:</b>	SMD, MLCC, Temperature Stable, Class II
<b>Features:</b>	Temperature Stable, Class II
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Failure Rate:</b>	N/A
<b>Miscellaneous:</b>	Note: Referee time for X5R dielectric for this part number is 48 hours

**Specifications**

<b>Capacitance:</b>	10 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	4 VDC
<b>Dielectric Withstanding Voltage:</b>	10 V
<b>Temperature Range:</b>	-55/+85C
<b>Temperature Coefficient:</b>	X5R
<b>Dissipation Factor:</b>	10%
<b>Aging Rate:</b>	5% Loss/Decade Hour
<b>Insulation Resistance:</b>	10 MOhms