

KEMET Part Number: C1210C104J1GACTU
(C1210C104J1GAC7800)

Ceramic, Commercial-(CxxxxC), 0.1 uF, 5%, 100 V, 1210, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I



General Information

Style:	SMD Chip
Series:	Commercial-(CxxxxC)
Chip Size:	1210
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Features:	Ultra-Stable, Low Loss, Class I
RoHS:	Yes
Termination:	Tin
Marking:	No
Failure Rate:	N/A

Dimensions

L	3.2mm +/-0.2mm
W	2.5mm +/-0.2mm
T	1.7mm +/-0.20mm
B	0.5mm +/-0.25mm

Packaging Specifications

Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	2000

Specifications

Capacitance:	0.1 uF
Capacitance Tolerance:	5%
Voltage DC:	100 VDC
Dielectric Withstanding Voltage:	250 V
Temperature Range:	-55/+125C
Temperature Coefficient:	C0G
Dissipation Factor:	0.1%
Aging Rate:	0% Loss/Decade Hour
Insulation Resistance:	10 GOhms