


Film, Metallized Polypropylene, Power, C4AT, 3.3 uF, 5%, 250 V, 70C, Lead Spacing = 27.5mm



Dimensions	
L	32mm NOM
H	22mm NOM
T	13mm NOM
S	27.5mm +/-0.4mm
LL	6mm -2mm

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	234

General Information	
Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	C4AT
Features:	Switching
RoHS:	Yes
Lead:	Wire Leads

Specifications	
Capacitance:	3.3 uF
Capacitance Tolerance:	5%
Voltage DC:	250 VDC
Voltage AC:	160 VAC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Dissipation Factor:	0.05%
Max dV/dt:	30 V
Resistance:	7.8 mOhms (100kHz)
Current:	10 Amps (100kHz 70C), 99 Amps (Peak)