


Film, Metallized Polypropylene, Power, C4C, 0.22 uF, 5%, 2,000 V, 630 V, 70C



Dimensions

D	23.5mm NOM
L	44mm NOM
LL	40mm +/-5mm

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	70

General Information

Dielectric:	Metallized Polypropylene
Style:	Axial
Series:	C4C
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Polyester Tape & Resin Protection

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage DC:	2000 VDC
Voltage AC:	630 VAC
Temperature Range:	-40/+85C
Rated Temperature:	70C
Dissipation Factor:	0.05%
Max dVdt:	700 V
Resistance:	8 mOhms (100kHz)
Current:	12 Amps (100kHz 70C), 154 Amps (Peak)