


**KEMET Part Number: FC0H105ZFTBR44-SS**  
(USCFC00H105ZZE)

Supercapacitors, SMD Can, Commercial Grade, FC, 1 F, -20/+80%, 5.5 V, V-Chip



Dimensions	
D	21mm +/-0.5mm
L	10.5mm MAX
W	21.6mm +/-0.2mm
S	10mm NOM
G	0mm +0.3/-0.1mm

Packaging Specifications	
Lead:	V-Chip
Packaging:	T&R, 380mm

General Information	
Series:	FC
Description:	Surface Mount Double Layer Capacitor
Features:	Ultra Low ESR, High Power Pulse
RoHS:	Yes

Specifications	
Capacitance:	1 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC, 4.2 VDC (Holding Voltage)
Temperature Range:	-25/+70C
Rated Temperature:	70C
Resistance:	7000 mOhms (1kHz)
Current:	1.5 mAmps (30min)