


KEMET Part Number: MPC0730LR20C
(UPIA0730LR20C0)

Power, MPC, 200 nH, 25%



Dimensions

Chip Size	3126
L	8mm MAX
W	6.7mm +/-0.3mm
T	4mm MAX
LL	1.5mm NOM
G	2mm +/-0.3mm

Packaging Specifications

Packaging:	T&R, 330mm
Packaging Quantity:	1000

General Information

Style:	SMD Chip
Series:	MPC
Description:	Shielded, Surface Mount Inductor
Features:	High Speed, Large Current DC/DC Converter
RoHS:	Yes
Core:	Composite

Specifications

Inductance:	0.2 uH (0.1 MHz)
Inductance Tolerance:	25%
Temperature Range:	-20/+120C
Shielded:	Yes
Current:	17500 mAmps (Isat, 20% Drop In Inductance), 23000 mAmps (Irms, 40C Rise By Self Heating)
DC Resistance:	1.2 mOhms