

**KEMET Part Number: PFR5332J100J12L4Bulk**  
(F411JK332J100C)

Film, Film/Foil Polypropylene, Commercial Grade, PFR/F411, 3300 pF, 5%, 100 V, 85C, Lead Spacing = 5mm



General Information	
<b>Dielectric:</b>	Film/Foil Polypropylene
<b>Style:</b>	Radial
<b>Series:</b>	PFR/F411
<b>Features:</b>	Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Miscellaneous:</b>	An Operating Temperature Up To +105C Is Allowed Under Certain Conditions. Please Consult Kemet For Details.

Dimensions	
<b>L</b>	7.2mm MAX
<b>H</b>	7mm MAX
<b>T</b>	5.5mm MAX
<b>S</b>	5mm -0.4mm
<b>LL</b>	4mm +1mm
<b>F</b>	0.5mm +/-0.05mm
<b>G</b>	0.5mm NOM

Specifications	
<b>Capacitance:</b>	3300 pF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	100 VDC
<b>Voltage AC:</b>	63 VAC
<b>Temperature Range:</b>	-55/+100C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	0.04% 1kHz, 0.05% 10kHz, 0.07% 100kHz
<b>Insulation Resistance:</b>	9090.9091 GOhms
<b>Max dVdt:</b>	1,000 V
<b>Inductance:</b>	6 nH

Packaging Specifications	
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	1000