

KEMET Part Number: PMR209MC6220M022R30
(P409CP224M250AH220)

Film, Metallized Paper, Resistor/Capacitor, PMR209/P409, 0.22 uF, 20%, 630 V, 85C, Lead Spacing = 20.3mm



General Information	
Dielectric:	Metallized Paper
Style:	Radial
Series:	PMR209/P409
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Construction:	Molded
Miscellaneous:	Not For New Design, Please Use The New P409 Series @ 275 VAC. Resistor= 22 Ohms

Dimensions	
L	24mm MAX
H	16.5mm MAX
T	11.3mm MAX
S	20.3mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	0.22 uF
Capacitance Tolerance:	20%
Voltage DC:	630 VDC
Voltage AC:	250 VAC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Insulation Resistance:	3 GOhms
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	150