

Film, Metallized Polypropylene, Commercial Grade, R71, 2.2 uF, 10%, 1,000 V, 105C, Lead Spacing = 27.5mm



Dimensions

L	32mm +0.3mm
H	33mm +0.1mm
T	18mm +0.2mm
S	27.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	128

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R71
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Above 105C DC And AC Voltage Derating Is 4%/C

Specifications

Capacitance:	2.2 uF
Capacitance Tolerance:	10%
Voltage DC:	1000 VDC
Voltage AC:	275 VAC
Temperature Range:	-40/+110C
Rated Temperature:	105C
Dissipation Factor:	0.1% 1kHz, 0.1% 10kHz, 0.1% 100kHz
Insulation Resistance:	13.6364 GOhms
Max dVdt:	180 V
Inductance:	18 nH