


**KEMET Part Number: SS11V-06180-CH**  
(UAL11V06180CH0, SS11V/H-06180-CH)

Commercial Grade, SS11V/H-CH, 0.018 H



**Dimensions**

<b>L</b>	22mm +/-1mm
<b>T</b>	14.5mm +/-1mm
<b>H</b>	21.5mm +/-1mm
<b>S</b>	10mm +/-0.5mm
<b>S1</b>	13mm +/-0.5mm
<b>LL</b>	3.5mm +/-1mm
<b>F</b>	0.8mm NOM

**Packaging Specifications**

<b>Weight:</b>	11.1 g
----------------	--------

**General Information**

<b>Style:</b>	Through-Hole Choke
<b>Series:</b>	SS11V/H-CH
<b>Description:</b>	Common Mode Filter
<b>RoHS:</b>	Yes
<b>Miscellaneous:</b>	Inductance Measurement Condition: 1kHz 1V KC530

**Specifications**

<b>Inductance:</b>	18000 uH
<b>Rated Temperature:</b>	120C
<b>Current:</b>	0.6 Amps
<b>Voltage AC:</b>	250 VAC
<b>DC Resistance:</b>	1.3 Ohms
<b>Insulation Resistance:</b>	100 MOhms