


Tantalum, MnO₂ Tantalum, Commercial Grade, T110, 33 uF, 10%, 10 V, 2.1 Ohms



Dimensions	
D	4.7mm +/-0.25mm
L	12.04mm +/-0.79mm
L2	15.49mm
LL	38.1mm +/-6.35mm
F	0.51mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk, Box
Packaging Quantity:	75

General Information	
Dielectric:	MnO ₂ Tantalum
Style:	Axial Hermetic
Series:	T110
Description:	Axial, Solid Tantalum, Hermetically Sealed, Military (Non-ER), Polar
Features:	Polar
RoHS:	Yes
Termination:	Tin
Lead:	Wire Leads, Uninsulated
Construction:	Hermetic
Notes:	When Supplied On T&R Or Ammo, Lead Length Is Determined By Taping Specification

Specifications	
Capacitance:	33 uF
Capacitance Tolerance:	10%
Voltage DC:	10 VDC (85C), 9 VDC (125C Surge), 0.1 V (125C Reverse)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Resistance:	2.1 Ohms (100kHz)
Leakage Current:	2 uAmps (25C)