


Tantalum, MnO2 Tantalum, Commercial Grade, T322, 10 uF, 20%, 35 V, 2 Ohms



General Information	
Dielectric:	MnO2 Tantalum
Style:	Axial
Series:	T322
Description:	Axial, Solid Tantalum, Molded, Military (Non-ER), Low ESR
Features:	Low ESR
RoHS:	Yes
Termination:	Tin
Lead:	Wire Leads, Uninsulated

Dimensions	
D	4.57mm MAX
L	10.67mm MAX
LL	38.1mm +/-6.35mm
F	0.51mm +/-0.05mm

Specifications	
Capacitance:	10 uF
Capacitance Tolerance:	20%
Voltage DC:	35 VDC (85C), 28 VDC (125C Surge), 0.35 V (125C Reverse)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Resistance:	2 Ohms (100kHz)
Leakage Current:	2.8 uAmps (25C)

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	100