

UL CAB UL CAB PC 302018 G



Sample photo

Order symbol: UL CAB PC 302018 G
Product nbr: 8143330
Description: UL Cabinet, PC
Remarks: Latches on the long side, smooth

EAN: 6418074053909
EI. number:
Finland:
Electric No. Denmark: 8212034031
Electric No. Italy: 7821015U

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:				Rating:
Length	Width	Height		
mm:	300	200	180	Ingress Protection (EN 60529): IP65
inch:	11.8	7.9	7.1	Impact Resistance (EN 62262): IK08
Materials:				Electrical insulation: Totally insulated
Material:	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
Base colour:	RAL 7035 -light grey			UV resistance: UL 508
Cover colour:	RAL 7035 -light grey			Flammability Rating: UL 746C 5"
Gasket material:	EPDM			UL Type:
Temperatures:				Glow Wire Test (IEC 695-2-1) °C: 960
Temperature °C (short term):	-40 ... 120 °C			Certificates:
Temperature °C (continuous):	-40 ... 80 °C			Germanischer Lloyd (GL)
Temperature °F (short term):	-40 ... 250 °F			Underwriters Laboratories
Temperature °F (continuous):	-40 ... 175 °F			SGS Fimko
				Lloyds Register of Shipping (LR)
				UL Canada
				Gost R

