

AR664CHSCF



Sample Photo

Including: Hinged screw cover base with 10-32 brass inserts, cover with formed in place PUR gasket, stainless hinge pin and 2 cover screws. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting. Plastic mounting flange.

Product #: 8561006
 Description: PC Enclosure
 Remarks: Hinged opaque screw cover with plastic mounting flange
 Package: 1
 Unit: PCS
 Product group:

EAN: 6418074066473
 ETIM: EC000261 EC000261

Support items:

[Product card \(PDF\)](#)
[Dimensional drawing \(mm\)](#)
[Cad-files \(registration needed\)](#)

Dimensions:	
Length (mm):	152.0
Width (mm):	152.0
Height (mm):	102.0
Length (inch):	6.0
Width (inch):	6.0
Height (inch):	4.0

Ratings:	
Ingress Protection (EN 60529):	IP66/67
Impact Resistance (EN 62262):	IK07/IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 508
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 4, 4X, 6, 6P, 12, 13

Materials:		Temperatures:	
Material:	Polycarbonate	Temperature °C (short term):	-40 ... 140 °C
Base colour:	RAL 7035 -light grey	Temperature °C (continuous):	-40 ... 80 °C
Cover screws material:	Stainless steel	Temperature °F (short term):	-40 ... 284 °F
Cover colour:	RAL 7035 -light grey	Temperature °F (continuous):	-40 ... 175 °F
Gasket material:	Polyurethane		

Data subject to change without notice