



### Main

Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	130 mm
IP degree of protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529
[Us] rated supply voltage	230 V AC
Light source	High luminosity LED, orange

### Complementary

Material	ABS (acrylonitrile butadiene-styrene) (body part) PC (globe)
CAD overall width	130 mm
CAD overall depth	130 mm
Product weight	0.99 kg
Marking	CE
Product mounting	By 3 M6 screws
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	22 mA
Flashing frequency	2.7 Hz
Clamping connection capacity	1.25 mm <sup>2</sup>
AWG gauge	AWG 18
Cable length	400 mm

### Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60947-1
Protective treatment	TC

Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-30...50 °C
Class of protection against electric shock	Class II conforming to IEC 61140

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0808 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available



### Contractual warranty

Warranty period	18 months
-----------------	-----------

Rotating Mirror Beacon

Dimensions

mm  
in.



Rotating Mirror Beacon

Panel Cut-out

