



### Main

Range of product	Harmony XB4 Harmony XB5
Product or component type	Block for test light
Product compatibility	Integral LED BA 9s
Light block type	Single block for test light function
[Us] rated supply voltage	12 V AC/DC 24 V AC/DC 24...120 V AC/DC
Electrical connection	1 wire

### Complementary

Class of protection against electric shock	Class I for Harmony XB4 conforming to IEC 60536 Class II for Harmony XB5 conforming to IEC 60536
Product weight	0.01 kg

### Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Standards	IEC 60947-1 EN 60947-5-1 CSA C22.2 No 14 EN 60947-5-5 EN 60947-1 IEC 60947-5-1 JIS C 4520 UL 508 EN 60947-5-4 IEC 60947-5-4 IEC 60947-5-5
Product certifications	GL UL listed LROS (Lloyds register of shipping) CSA

RINA  
BV  
DNV

---

Vibration resistance	5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn for 18 ms conforming to IEC 60068-2-27 50 gn for 11 ms conforming to IEC 60068-2-27

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---

---

## Wiring Diagram

---

