




Purchase

APC
 AP7900

Overview

Model Name	Rack PDU, Switched, 1U, 15A, 100/120V, (8)5-15
Includes	Cord retention bracket(s), Horizontal mounting brackets, Installation guide, User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Antigua And Barbuda, Anguilla, Netherlands Antilles, Argentina, Aruba, Barbados, Bermuda, Bolivia, Bahamas, Belize, Canada, Chile, Colombia, Costa Rica, Cuba, Dominica, Dominican Republic, Ecuador, Falkland Islands (Malvinas), Grenada, Guatemala, Guyana, Honduras, Haiti, Jamaica, Japan, SAINT KITTS AND NEVIS, Cayman Islands, SAINT LUCIA, Mexico, Nicaragua, Panama, Peru, Puerto Rico, Paraguay, El Salvador, Trinidad And Tobago, Taiwan, United States, Uruguay, SAINT VINCENT AND THE GRENADINES, Venezuela, VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	15 A
Output Connections	(8) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	100V, 120V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	12 A
Input Connections	NEMA 5-15P
Cord Length	3.66 meters
Number of Power Cords	1
Acceptable Input Voltage	100-120 VAC
Maximum Input Current per phase	15 A

Load Capacity	1440 VA
---------------	---------

Physical

Net Weight	2.27 kg
Maximum Height	44 mm
Maximum Width	445 mm
Maximum Depth	108 mm
Shipping Weight	3.45 kg
Shipping Height	70 mm
Shipping Width	470 mm
Shipping Depth	343 mm
Color	Black

Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CUL Listed , FCC Part 15 Class A , ICES-003 , UL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant
Battery Notes	Battery Notes