



Main

| | |
|------------------------------------|----------------------|
| Range | TeSys |
| Product or component type | Terminal block |
| Device short name | LA7K |
| Accessory / separate part category | Connection accessory |
| Mounting support | Rail |
| Product compatibility | LR7K LR2K |

Complementary

| | |
|-------------------------|--|
| Connections - terminals | Screw clamp terminals 1 cable(s) 1.5...4 mm ² - cable stiffness: solid Screw clamp terminals 1 cable(s) 0.75...4 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 0.34...2.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable(s) 1.5...4 mm ² - cable stiffness: solid Screw clamp terminals 2 cable(s) 0.75...4 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable(s) 0.34...1.5 mm ² - cable stiffness: flexible - with cable end |
| Tightening torque | 1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm |
| Height | 80 mm |
| Width | 45 mm |
| Depth | 75 mm |
| Product weight | 0.1 kg |
| Quantity per set | Set of 10 |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|