

ZCKE09

limit switch head ZCKE - w/o lever stay put left
and right actuation



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product compatibility	XCKJ
Associated lever	ZCKY71 ZCKY61
Associated body	ZCKJ11 ZCKJ9H29 ZCKJ1 ZCKJ11H29 ZCKJD31 ZCKJ9H7 ZCKJ21 ZCKJ2 ZCKJD31H7 ZCKJ1H7 ZCKJD39 ZCKJ1H29 ZCKJ2H7 ZCKJ21H29 ZCKJ9 ZCKJ2H29 ZCKJD39H7 ZCKJ21H7 ZCKJD39H29 ZCKJD31H29 ZCKJ11H7
Movement of operating head	Rotary
Type of operator	Stay put without operating lever stay put
Type of approach	Lateral approach 2 directions

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Switch actuation	From left and right
Positive opening	With
Head material	Metal

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------