



Overview

Model Name	APC Smart-ups 750VA LCD RM 2U 120V
Includes	CD with software , Documentation CD , Installation guide , Rack Mounting support rails , Smart UPS signalling RS-232 cable , USB cable
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Canada , United States

Output

Output Power Capacity	500 Watts / 750 VA
Max Configurable Power (Watts)	500 Watts / 750 VA
Nominal Output Voltage	120V
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Sine wave
Output Connections	(6) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	2.44 meters
Input voltage range for main operations	82 - 144 V
Input voltage adjustable range for mains operation	75 - 154V
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	0

Battery Slots Empty	0
Typical recharge time	3 hour(s)
Replacement Battery	APCRBC123
RBC Quantity	1

Communications & Management

Interface Port(s)	SmartSlot , USB
Available SmartSlot™; Interface Quantity	1
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

Surge Protection and Filtering

Surge energy rating	459 joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	89.0 mm
Maximum Width	432.0 mm
Maximum Depth	406.0 mm
Rack Height	2 U
Net Weight	17.27 kg
Shipping Weight	21.23 kg
Shipping Height	241.0 mm
Shipping Width	546.0 mm
Shipping Depth	584.0 mm
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	16.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	42.000 dB
Online Thermal Dissipation	46.000 BTU/hr

Conformance

Approvals	CSA , FCC Part 15 Class A , UL 1778
Standard warranty	3 years repair or replace (excluding battery) and 2 year for battery
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs