



### Purchase

APC  
 PER7

### Overview

Model Name	APC Personal SurgeArrest, 7 outlet
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Mexico , United States

### Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	1.83 meters

### Surge Protection and Filtering

Surge energy rating	240 joules
Data Line Protection	--

### Physical

Maximum Height	51 mm
Maximum Width	108 mm
Maximum Depth	267 mm
Net Weight	0.77 kg
Shipping Weight	0.95 kg
Shipping Height	53 mm
Shipping Width	184 mm
Shipping Depth	324 mm

Master Carton Units	12.0
Master Carton Weight	26.4 lbs
Color	Beige
SCC Codes	10731304000119
Units per Pallet	192.0

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

### Conformance

Approvals	CSA , UL 1283 , UL 1363 , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000

### Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs