



Overview

Model Name	APC Power Saving Back-UPS Pro 1500
Includes	CD with software , USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Madagascar , Mauritius , Mayotte , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Reunion , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	865 Watts / 1500 VA
Max Configurable Power (Watts)	865 Watts / 1500 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Output Connections	(5) NEMA 5-15R (Battery Backup) , (5) NEMA 5-15R (Surge Protection)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	1.83 meters
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	8 hour(s)
Replacement Battery	APCRBC124

RBC Quantity	1
--------------	---

Communications & Management

Interface Port(s)	USB
Available SmartSlot™ Interface Quantity	0
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	354 joules
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: instantaneous
Data Line Protection	Cable modem / Video protection , Network line - 10/100/1000 Base-T Ethernet (RJ-45 connector)

Physical

Maximum Height	301.0 mm
Maximum Width	112.0 mm
Maximum Depth	382.0 mm
Rack Height	0 U
Net Weight	12.1 kg
Shipping Weight	13.35 kg
Shipping Height	387.0 mm
Shipping Width	238.0 mm
Shipping Depth	488.0 mm
Master Carton Units	1.0
Master Carton Weight	0.0 lbs
SCC Codes	1073130426877 9
Units per Pallet	20.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-9000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	45.000 dB

Conformance

Approvals	ENERGY STAR (USA) , FCC Part 15 Class B , NOM , TUV , UL 1778
Standard warranty	3 years repair or replace
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs