

KEMET Part Number: FG0H224ZF
(USCFG00H224Z00)

Supercapacitors, Radial Pin, Commercial Grade, FG, 0.22 F, -20/+80%, 5.5 V, Pin Leads, Lead Spacing = 5.08mm



Dimensions

Dimensions	
D	13mm +/-0.5mm
L	9mm MAX
S	5.08mm +/-0.5mm
LL Negative	2.5mm MIN
LL Positive	2.2mm MIN

Packaging Specifications

Lead:	Pin Leads
Packaging:	Bulk

General Information

Series:	FG
Description:	Radial Cylindrical Double Layer Capacitor
RoHS:	Yes
Miscellaneous:	DischargeValue = 0.28 F

Specifications

Capacitance:	0.22 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70C
Resistance:	100000 mOhms (1kHz)