

1U Rack-Mount Power Strip, 120V, 20A, 5-20P, 12 Outlets (6 Front-Facing, 6-Rear-Facing) 15-ft. Cord

MODEL NUMBER: RS-1215-20



Highlights

- Designed for standard 19-inch racks (1U high)
- 12 outlets (6 front / 6 rear)
- 15 ft. cord
- 20-amp circuit breaker

Package Includes

- RS-1215-20
- Warranty information
- Instruction manual

Description

Tripp Lite's RS-1215-20 Power Strip offers 20 amp capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-20 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA5-20R outlets (6 front/6 rear), 15 ft AC power cord and lighted switch with cover prevents risk of accidental turn-off.

PLUG/OUTLET: Input: NEMA 5-20P

Output: 12 NEMA5-20R (6 front & 6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 20A (Requires NEMA 5-20R wall receptacle)

FORMAT: 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 NEMA5-20R output receptacles (6 front/6 rear)
- 15 foot AC cord NEMA5-20P plug connection
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn off
- 20 amp electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15/20R
Circuit Breaker (amps)	20
Outlet Orientation	6 front facing / 6 rear facing
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Connection Type	NEMA 5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Red illuminated 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Dimensions (hwd / cm)	4.445 x 44.45 x 11.4
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.09
Material of Construction	Sheet metal
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	1U rackmount, wall-mount and undercounter installation supported
Outlets Measurement (Center to Center)	Distance between Front outlets = 51.6mm; Distance between Rear outlets = 71.1mm
SPECIAL FEATURES	
TVSS Grounding	Back panel nut and bolt grounding lug
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363 (UR status)
cUL / CSA (Canada)	cUL



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>