

Heavy-Duty Power Extension Cord, 16A (IEC309 to C19), 10-ft.

MODEL NUMBER: P070-010



Highlights

- 10ft IEC309 (2P+G) to C19 Power Cord
- 16A, 250V rated
- RoHS Compliant

Package Includes

- 10ft, IEC 309 to C19 Power Cord

Description

10ft, IEC 309 (2P+ Ground) to C19 power cable. 16 Amp, 90 - 250 VAC range. RoHS compliant.

Features

- 10ft IEC 309 to C19 Power cord
- 16A, 250V rated
- H05VV-F 1.5mm² x 3G Cable

Specifications

INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.1
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	IEC-320-C19
Side B - Connector 1	IEC-309 16A 2P+E
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>