

VGA Monitor Y Splitter Cable (HD15 M/2xF), 1-ft.

MODEL NUMBER: **P516-001**



Highlights

- Splits the VGA/XVGA signal providing simultaneous display of the same image on two monitors
- HD15 Male splits to 2 HD15 Female

System Requirements

- PC/MAC with 15-pin Female VGA CPU port

Package Includes

- 1-ft VGA/XVGA Splitter Cable

Description

Tripp Lite's 1-ft. VGA/XVGA Monitor "Y" Splitter cable provides an inexpensive alternative for splitting the video signal from your PCs VGA port to two monitors (up to 800 x 600) that use standard 15-pin plugs. Perfect for laptops to display on a separate, larger monitor. Use for short distance applications only. For higher resolution monitors, use [P516-001-HR](#). For applications that require longer distances and highest resolution, see Tripp Lite [B114-002-R](#), powered 2-Port Splitter, or, [B114-004-R](#), powered 4-Port Splitter.

Features

- HD15 Male to 2 x HD15 Female w/Hex Nuts
- Molded, double-shielded construction for maximum EMI/RFI protection
- Two monitors display the image from one PC
- Inexpensive solution for presentations

Specifications

INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.3
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>