

## Cat5e 350MHz Outdoor-Rated Molded Patch Cable, (RJ45 M/M) - Gray, 100-ft.

MODEL NUMBER: N007-100-GY



### Highlights

- High Quality Outdoor Rated PVC Jacket
- Molded, Snagless RJ45 Connector

### Package Includes

- 100ft Outdoor Rated Cat5e Patch Cable

### Description

Tripp Lite's line of Outdoor Rated Cat5e patch cables are manufactured with high quality UV (Ultra Violet) resistant PVC cable. With an Operating Temperature range of -40C to +60C (-40F to +140F), this 100ft cable handles a wide range of weather conditions, most importantly, the degrading effects of Ultra Violet rays. Molded, snagless connectors provide a secure connection every time. Cables meet EIA/TIA 568-B.2, and are UL verified to Category 5e.

### Features

- UV (Ultra Violet) Resistant Gray PVC jacket
- CMR, CMX, and UL444 Rated
- EIA/TIA 568-B.2 Compliant
- UL Verified Category 5e
- Molded, Snagless Connectors
- 4pr, Solid Conductors for long distance signal integrity

## Specifications

INPUT	
Cable Length (ft.)	100
Cable Length (m)	30.5
PHYSICAL	
Color	Gray
CONNECTIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL Verified Category 5e,CMR, CMX, and UL444 Rated, EIA/TIA 568-B.2 Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>