

Protect It! 6-Outlet Low-Profile Surge Protector, Direct Plug-In, 540 Joules, Diagnostic LED

MODEL NUMBER: SK6-0



Highlights

- 6 outlets/direct plug-in
- 540 joule rating
- \$10,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Package Includes

- SK6-0 Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0 Surge Suppressor from Tripp Lite is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features 6 outlets and 540 joules of surge energy absorption. \$10,000 Ultimate Lifetime Insurance (USA & Canada only).

Features

- 6 outlets; direct plug-in
- Surge energy absorption: 540 joules; 27,000 amps
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

| OUTPUT | |
|------------------------------------|---------------------------------------|
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (6) 5-15R |
| Output (Watts) | 1800 |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | Holds up to 4 large transformer plugs |
| Right-Angle Outlets | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |



| | |
|-------------------------------------|--|
| Input Connection Type | NEMA 5-15P input plug |
| Input Cord Length (ft.) | 0 |
| Input Cord Length (m) | 0.00 |
| Input Cord Length Details | Direct Plug-In |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 36000 |
| Right-Angle Plug | No |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 540 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 150V |
| AC Suppression Surge Current Rating | 27,000 amps |
| UL1449 Let Through Rating | 400, 500, 500 |
| Immunity | Conforms to IEE 587 / ANSI C62.41 |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 1.18 x 4.53 x 4.75 |
| Shipping Dimensions (hwd / cm) | 3 x 11.5 x 12 |
| Shipping Weight (lbs.) | .55 |
| Shipping Weight (kg) | .25 |
| Unit Dimensions (hwd / in.) | 4.80 x 4.35 x 1.42 |
| Unit Dimensions (hwd / cm) | 12.19 x 11.05 x 3.6 |
| Unit Weight (lbs.) | .406 |
| Unit Weight (kg) | .18 |
| Material of Construction | Plastic |
| Integrated Keyhole Mounting Tabs | Direct plug-in suppressor mounts directly to a wall receptacle |
| Housing Color | Light Gray |
| Receptacle Color | Light Gray |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Outlets Measurement (Center to Center) | Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd Edition |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$10,000 Ultimate Lifetime Insurance |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>