

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0731375003**  
**Status:** **Active**  
**Overview:** BNC RF Connectors  
**Description:** BNC 50 Ohm, Right-Angle PCB Bulkhead Jack Receptacle, Panel Isolated, Black PBT Housing, Housing Height 13.20mm, Nut and Lockwasher included

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification SD-73137-5003-PKG \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E107635

**General**

Product Family RF/Coax Connectors  
 Series 73137  
 Overview BNC RF Connectors  
 Product Name BNC  
 Style PCB  
 UPC 800753750258  
 Wire/Cable Type N/A

**Physical**

Cable Attachment N/A  
 Flammability 94V-0  
 Gender Jack  
 Keying to Mating Part None  
 Net Weight 15.347/g  
 Orientation Right Angle  
 PCB Mounting Through Hole  
 PCB Thickness - Recommended 3.20mm  
 Packaging Type Tray  
 Panel Mount Yes  
 Panel Mount Method Bulkhead

**Electrical**

Impedance 50Ω

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 010  
 Lead-free Process Capability WAVE  
 Max. Cycles at Max. Process Temperature 001  
 Process Temperature max. C 245

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification SD-73137-5003-PKG  
 Sales Drawing SD-73137-5003



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - ED/30/2017 (7 July 2017)  
 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS 50 Image  
 ELV Not Relevant  
 RoHS Phthalates Not Contained

**Search Parts in this Series**

[73137 Series](#)