

MNX PC 95/60 HT



Sample photo

Order symbol: PC 95/60 HT
Product nbr: 6011931
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074054678
EI. number:
 Finland: 3421372
 Electric No. 8212027747
 Denmark:
 Electric No. Sweden: 6011931

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions: Length Width Height **Accessories:**

mm:	100	100	60	MIN 8	DIN-15 Mounting rail
inch:	3.9	3.9	2.4	B-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

Materials: **Rating:**

Material: Polycarbonate	Ingress Protection (EN 60529): IP66/IP67
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: Smoked grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Black	UV resistance: UL 508
Gasket material: Polyurethane	Flammability Rating: UL 746C 5"
	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures: **Certificates:**

Temperature °C (short term): -40 ... 120 °C	Germanischer Lloyd (GL)
Temperature °C (continuous): -40 ... 80 °C	SGS Fimko
Temperature °F (short term): -40 ... 250 °F	Gost R
Temperature °F (continuous): -40 ... 175 °F	

Accessories:

MIV 95 Mounting plate (Galvanized steel)

