

CAB CAB PC 604022 T



Sample photo

Order symbol: CAB PC 604022 T
Product nbr: 8113070
Description: Cabinet, PC
Remarks: Latches on the long side

EAN: 6418074020451
EI. number:
 Finland: 3424176
 Electric No. Denmark: 8212020294
 Electric No. Italy: 7822065
 Electric No. Sweden: 2539957

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	600	400	220	EKIV 37	DIN-35 Mounting rail
inch:	23.6	15.7	8.7	DS35370E1	DIN-35 Mounting rail
Materials:				FP A 64	Swing-out door/Front plate
Material:	Polycarbonate			MB 12225 AL	Swing door set
Base colour:	RAL 7035 -light grey			FP 64	Front plate
Cover colour:	Smoked grey			FP 18x3-64	Front plate
Gasket material:	Polyurethane			DRF 63/64	DIN rail frame set
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP65	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
EKIV 64H	Mounting plate			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Lloyds Register of Shipping (LR)	
				Gost R	

