



Sample photo

Order symbol: CAB ABS 302018 G3B
Product nbr: 8183332
Description: Cabinet, ABS, Grey door
Remarks: Lock on the long side

EAN: 6418074020109
EI. number:
 Finland: 3424305
 Electric No. Denmark: 8212019001
 Electric No. Italy: 7811020
 Electric No. Sweden: 2540065

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions: | | Length | Width | Height | Accessories: | |
|-------------------------------------|--|----------------------|-------|--------|------------------------------------------|----------------------------|
| mm: | | 300 | 200 | 180 | EKIV 17 | DIN-35 Mounting rail |
| inch: | | 11.8 | 7.9 | 7.1 | DS35170E1 | DIN-35 Mounting rail |
| Materials: | | | | | EKIV 27 | DIN-35 Mounting rail |
| Material: | | ABS | | | DS35270E1 | DIN-35 Mounting rail |
| Base colour: | | RAL 7035 -light grey | | | FP A 23 | Swing-out door/Front plate |
| Cover colour: | | RAL 7035 -light grey | | | MB 12225 AL | Swing door set |
| Gasket material: | | Polyurethane | | | FP 23 | Front plate |
| Temperatures: | | | | | FP 12-23 | Front plate |
| Temperature °C (short term): | | -40 ... 80 °C | | | DRF 23 | DIN rail frame set |
| Temperature °C (continuous): | | -40 ... 60 °C | | | Rating: | |
| Temperature °F (short term): | | -40 ... 175 °F | | | Ingress Protection (EN 60529): IP65 | |
| Temperature °F (continuous): | | -40 ... 140 °F | | | Impact Resistance (EN 62262): IK08 | |
| Accessories: | | | | | Electrical insulation: Totally insulated | |
| EKIV 23 | | Mounting plate | | | Halogen free (DIN/VDE 0472, Part 815): 1 | |
| | | | | | Flammability Rating: UL 94 HB | |
| | | | | | Glow Wire Test (IEC 695-2-1) °C: 650 | |
| | | | | | NEMA Class: NEMA 1, 4, 4X, 12, 13 | |
| | | | | | Certificates: | |
| | | | | | SGS Fimko | |
| | | | | | Gost R | |

