



Sample photo

**Order symbol:** CAB ABS 403018 T3B  
**Product nbr:** 8183052  
**Description:** Cabinet, ABS  
**Remarks:** Locks on the long side

**EAN:** 6418074020314  
**EI. number:**  
 Finland: 3424368  
 Electric No. Denmark: 8212019056  
 Electric No. Italy: 7812045  
 Electric No. Sweden: 2540045

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:
mm:	400	300	180	EKIV 43 PL Mounting plate, Plastic
inch:	15.7	11.8	7.1	EKIV 27 DIN-35 Mounting rail

Materials:	
<b>Material:</b>	ABS
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover colour:</b>	Smoked grey
<b>Gasket material:</b>	Polyurethane

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 80 °C
<b>Temperature °C (continuous):</b>	-40 ... 60 °C
<b>Temperature °F (short term):</b>	-40 ... 175 °F
<b>Temperature °F (continuous):</b>	-40 ... 140 °F

Accessories:	
EKIV 43	Mounting plate

DS35270E1	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
DS35370E1	DIN-35 Mounting rail
FP A 43	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 43	Front plate
FP 12x2-43	Front plate
FP 12x3-43	Front plate
DRF 43/44	DIN rail frame set

Rating:
Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
Flammability Rating: UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:
SGS Fimko
Gost R

