

**MNX PC 200/88 XHT**



Sample photo

**Order symbol:** PC 200/88 XHT  
**Product nbr:** 6013930  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074051943  
**El. number:**  
 Finland: 3435266  
 Electric No. Denmark: 8212023071  
 Electric No. Sweden: 6013930

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	255	180	88	MIN 15 DIN-15 Mounting rail
inch:	10.0	7.1	3.5	MIN 20 DIN-15 Mounting rail
				MIV 15 DIN-35 Mounting rail
				MIV 20 DIN-35 Mounting rail

Materials:	
<b>Material:</b>	Polycarbonate
<b>Base colour:</b>	RAL 7035 -light grey
<b>Cover screws material:</b>	Polyamide
<b>Cover colour:</b>	Smoked grey
<b>Cover screws colour:</b>	Black
<b>Gasket material:</b>	Polyurethane

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C
<b>Temperature °C (continuous):</b>	-40 ... 80 °C
<b>Temperature °F (short term):</b>	-40 ... 250 °F
<b>Temperature °F (continuous):</b>	-40 ... 175 °F

Accessories:	
MIV 200	Mounting plate (Galvanized steel)

Certificates:
Germanischer Lloyd (GL)
SGS Fimko
Gost R

