



**Order symbol:** TA201610T  
**Product nbr:** 5814006  
**Description:** Enclosure, ABS  
**Remarks:** Clear transparent cover

**EAN:** 6418074060785  
**EI. number:**  
 Finland: 3435694  
 Electric No. Denmark: 8212035030  
 Electric No. Sweden: 5814006

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	201	163	98	DH-3 DIN-35 Mounting rail
inch:	7.9	6.4	3.9	ARH 2320 DIN-35 Mounting rail
<b>Materials:</b>				FP 10674 DPS 14553 Grey sealing plug set
<b>Material:</b>	ABS			<b>Rating:</b>
<b>Base colour:</b>	RAL 7035 -light grey			Ingress Protection (EN 60529): IP65
<b>Cover screws material:</b>	Polyamide			Impact Resistance (EN 62262): IK07
<b>Cover colour:</b>	Clear transparent			Electrical insulation: Totally insulated
<b>Cover screws colour:</b>	Grey			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Gasket material:</b>	Polyurethane			Flammability Rating: UL 94 HB
<b>Temperatures:</b>				Glow Wire Test (IEC 695-2-1) °C: 650
<b>Temperature °C (short term):</b>	-40 ... 80 °C			<b>Certificates:</b>
<b>Temperature °C (continuous):</b>	-40 ... 60 °C			SGS Fimko
<b>Temperature °F (short term):</b>	-40 ... 175 °F			
<b>Temperature °F (continuous):</b>	-40 ... 140 °F			
<b>Accessories:</b>				
MP 2016	Mounting plate			

TEMPO 201x163x98

