

**SOLID PC 1919 13 G-2FSH**



Sample photo

**Order symbol:** PC 1919 13 G-2FSH  
**Product nbr:** 2539505  
**Description:** Enclosure, PC  
**Remarks:** Grey hinged cover

**EAN:** 6418074052704  
**EI. number:**  
**Finland:** 3435722  
**Electric No. Sweden:** 2539505

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	188	188	130	EKHXT	Mounting plate isolated
inch:	7.4	7.4	5.1	EKV 12	DIN-35 Mounting rail

Materials:		Rating:	
<b>Material:</b>	Polycarbonate	Ingress Protection (EN 60529): IP65	
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08/IK09	
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated	
<b>Cover colour:</b>	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Grey	UV resistance: UL 508	
<b>Gasket material:</b>	Polyurethane	Flammability Rating: UL 746C 5"	
		Glow Wire Test (IEC 695-2-1) °C: 960	

Temperatures:		Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C	SGS Fimko	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	Gost R	
<b>Temperature °F (short term):</b>	-40 ... 250 °F		
<b>Temperature °F (continuous):</b>	-40 ... 175 °F		

Accessories:	
EKHVT	Mounting plate

