

SOLID PC 2819 13 G



Sample photo

Order symbol: PC 2819 13 G
Product nbr: 5330360
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005441
EI. number:
 Finland: 3423705
 Electric No. Italy: 7401020
 Electric No. Sweden: 2539410

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions: Length Width Height Accessories:

Dimensions:	Length	Width	Height	Accessories:	
mm:	278	188	130	EKJXT	Mounting plate isolated
inch:	10.9	7.4	5.1	EKV 12	DIN-35 Mounting rail
				EKV 22	DIN-35 Mounting rail
				EKJZR	Extension frame

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08/IK09
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Certificates:

SGS Fimko
 Gost R

Accessories:

EKJVT	Mounting plate
-------	----------------

