

SOLID PC 2828 13 T



Sample photo

Order symbol: PC 2828 13 T
Product nbr: 5330062
Description: Enclosure, PC
Remarks: Transparent cover

EAN: 6418074005519
EI. number:
 Finland: 3423813
 Electric No. Italy: 7402040
 Electric No. Sweden: 2539448

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	278	278	130	EKOXT	Mounting plate isolated
inch:	10.9	10.9	5.1	EKV 22	DIN-35 Mounting rail
				EKOZR	Extension frame

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Clear transparent
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08/IK09
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Certificates:
SGS Fimko
Gost R

Accessories:	
EKOVT	Mounting plate

