



Amphenol Aerospace
 40-60 Delaware Avenue
 Sidney, NY 13838-1395
Phone: 800-678-0141 - **Fax:** 607-563-5157
Email: info@amphenol-aerospace.com
Website: www.amphenol-aerospace.com

Joe Ryder
 Product Line Manager
 Core Products
Phone: 607-563-5001
Email: jryder@amphenol-ao.com

Specifications

Connector Type	D38999/
Shell Style	Jam Nut Receptacle
Shell Material	Aluminum
Shell Finish	Electroless Nickel
Insulation Resistance	5000 megohms min. @500 VDC25C
Operating Temperature [Min]	-65°C
Operating Temperature [Max]	+200°C
Shielding Effectiveness	65dB@10GHz
Durability	48 Hour Salt Spray
Contact Type	A
Contact Description	Less Pins

Contacts

Insert Arrangement	
Front Face of Pin Insert Shown	
Shell Size	J
Insert Arrg	20
Service Rating	N
Total # Contacts	30
Test Current	(20)7.5 AMPS, (16)13 AMPS, (12)23 AMPS, (8)46 AMPS
Wire Size for 20	24, 22, 20
Wire Size for 12	14, 12
Contact Size 20	10
Number of Contacts	
Contact Size 16	13
Number of Contacts	
Contact Size 12 Coax	4
Number of Contacts	
Contact Size 8 Twinax	3
Number of Contacts:	