

MNX PCM 125/100 G



Sample photo

Order symbol: PCM 125/100 G
Product nbr: 6016309
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038050
EI. number:
 Finland: 3421637
 Electric No. 8212027103
 Denmark:
 Electric No. Italy: 7341030
 Electric No. Sweden: 2535318

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	130	130	100	MIN 10	DIN-15 Mounting rail
inch:	5.1	5.1	3.9	MIV 10	DIN-35 Mounting rail
Materials:				FP A 125/130	Front plate (Aluminium)
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Polyamide				
Cover colour:	RAL 7035 -light grey				
Cover screws colour:	Grey				
Gasket material:	TPE				
Temperatures:				Rating:	
Temperature °C (short term):	-40 ... 120 °C			Ingress Protection (EN 60529): IP66/IP67	
Temperature °C (continuous):	-40 ... 80 °C			Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 250 °F			Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
MIV 125	Mounting plate (Galvanized steel)			Flammability Rating: UL 746C 5"	
				Glow Wire Test (IEC 695-2-1) °C: 960	
				NEMA Class: NEMA 1, 4, 4X, 6	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

