
EAO – Your Expert Partner for **Human Machine Interfaces**

704.403.018 - Selector switch actuator 3 positions, short lever

704.403.018 - Selector switch actuator 3 positions, short lever



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

 $\begin{array}{ll} \mbox{Mounting cut-out} & \mbox{\varnothing 30,5$ mm} \\ \mbox{Design} & \mbox{flush} \\ \end{array}$

Front

Front dimension Ø 35 mm
Front shape round
Front bezel colour natural anodized
Front bezel material Aluminium

Other Attributes

Weight 0.056 kg

Operating-/Indication part

Lever material Plastic Lever colour black

Switching angle

Lever illumination non-illuminative

Lever shape short

IP-Rating

Front protection IP65

Actuator

Switching action

Switching element

Rotary positions 3 max. number of switching 3 elements

Function


Selector switch

eao 🔳

EAO – Your Expert Partner for **Human Machine Interfaces**


704.403.018 - Selector switch actuator 3 positions, short lever

Dimensions



X = Screw terminal

Mounting cut-outs



PIT = Push-in terminal

Wiring diagram



Switching positions



Additional information

Max. 3 switching elements can be clipped on The colour of anodized aluminium parts can vary due to technical production reasons

Legend

Switching action: A = Rest, C = Maintained

eao 🔳